

HALDER**SIMPLEX soft-faced hammer without inserts, with handle, Body Ø / Material: 50Gmm****Order data**

Order number	753300 50G
GTIN	2050001008442
Item class	73W

Description**Version:**

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft mallets and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Striking face Ø of the inserts	50 mm
Head length with inserts	135 mm
Material of body	Cast steel
Handle length	310 mm
Overall length	365 mm

Body Ø	50 mm
Series	SIMPLEX soft-faced hammer
Type of product	Soft-faced hammer housing

Accessories

SIMPLEX soft-faced hammer, spare handle for body Ø 50 mm	753400 50
SIMPLEX soft-faced hammer, soft metal insert for Hammer head Ø 50 mm	754000 50
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 50 mm	753600 50
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 50 mm	753700 50
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 50A mm	753310 50A
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 50G mm	753310 50G
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 50 mm	753500 50
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 50 mm	753450 50