

 **HALDER**
SIMPLEX soft-faced hammer without inserts, with handle, Body Ø / Material: 60Gmm


Order data

Order number	753300 60G
GTIN	2050001004611
Item class	73W

Description

Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft mallets and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Body Ø	60 mm
Material of body	Cast steel
Handle length	340 mm
Striking face Ø of the inserts	60 mm
Head length with inserts	145 mm

Overall length	405 mm
Series	SIMPLEX soft-faced hammer
Type of product	Soft-faced hammer housing

Accessories

SIMPLEX soft-faced hammer, soft metal insert for Hammer head Ø 60 mm	754000 60
SIMPLEX soft-faced hammer, spare handle for body Ø 60 mm	753400 60
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 60 mm	753450 60
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 60 mm	753700 60
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 60 mm	753500 60
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 60 mm	753600 60
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 60G mm	753310 60G