

 **HALDER**
SIMPLEX soft-faced hammer with soft metal inserts, silver, Body Ø / Material: 60Gmm

Order data

Order number	753200 60G
GTIN	4030618300304
Item class	73W

Description
Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Weight	1.95 kg
Overall length	405 mm
Material of body	Cast steel
Striking face Ø of the inserts	60 mm
Head length with inserts	145 mm

Handle length	340 mm
Material of the handle	wood
Series	SIMPLEX soft-faced hammer
Material of insert	Soft metal, hard
Manufacturer's designation	SIMPLEX
Colour	silver
Type of product	Hammer

Accessories

SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 60G mm	753310 60G
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 60 mm	753450 60
SIMPLEX soft-faced hammer, spare handle for body Ø 60 mm	753400 60
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 60 mm	753600 60
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 60 mm	753700 60
SIMPLEX soft-faced hammer, soft metal insert for Hammer head Ø 60 mm	754000 60
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 60 mm	753500 60