

 **HALDER**
SIMPLEX soft-faced hammer with soft metal inserts, silver, Body Ø / Material: 60Gmm

Order data

Order number	753200 60G
GTIN	4030618300304
Item class	73W

Description
Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Weight	1.95 kg
Overall length	405 mm
Material of body	Cast steel
Striking face Ø of the inserts	60 mm
Head length with inserts	145 mm

Handle length	340 mm
Material of the handle	wood
Series	SIMPLEX
Material of insert	Soft metal, hard
Colour	silver
Type of product	Hammer

Accessories

SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 60G mm	753310 60G
SIMPLEX soft-faced hammer, spare handle for body Ø 60 mm	753400 60
SIMPLEX soft-faced hammer, soft plastic TPE insert for Hammer head Ø 60 mm	753450 60
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 60 mm	753500 60
SIMPLEX soft-faced hammer, plastic insert for Hammer head Ø 60 mm	753600 60
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 60 mm	753700 60
SIMPLEX soft-faced hammer, soft metal insert for Hammer head Ø 60 mm	754000 60