

 **HALDER**
SIMPLEX soft-faced hammer without inserts, with handle, Body Ø / Material: 80Gmm


Order data

Order number	753300 80G
GTIN	2050001008459
Item class	73W

Description

Version:

Sturdy, two-piece clamp housing with two exchangeable striking inserts. Suitable inserts are available for various types of work.

All insert types can also be combined with each other.

Soft mallets and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Soft-faced hammers and driving mallets: Aluminium or annealed cast iron housing; wooden handle.

Application:

Size **A** = **Aluminium housing:** For light work, e.g. positioning.

Size **G** = **Annealed cast iron housing:** For heavy, powerful blows, e.g. driving machine parts into position etc.

Spare part:

Spare handle available under No. 753400 and soft-faced hammer housing under No. 753310.

Note:

Size codes **A** = Aluminium housing; **G** = Annealed cast iron housing.

Technical description

Material of body	Cast steel
Body Ø	80 mm
Overall length	490 mm
Head length with inserts	165 mm
Striking face Ø of the inserts	80 mm

Handle length	400 mm
Series	SIMPLEX soft-faced hammer
Type of product	Soft-faced hammer housing

Accessories

SIMPLEX soft-faced hammer, spare handle for body Ø 80 mm	753400 80
SIMPLEX soft-faced hammer housing without inserts, without handle for body Ø / material 80G mm	753310 80G
SIMPLEX soft-faced hammer, super-plastic insert for Hammer head Ø 80 mm	753700 80
SIMPLEX soft-faced hammer, spare handle for body Ø 80L mm	753400 80L
SIMPLEX soft-faced hammer, rubber composition insert for Hammer head Ø 80 mm	753500 80