



“HF” bit for Torx®, 1/4 inch E 6.3 with retainer function, Torx® profile: TX10



Order data

Order number	674255 TX10
GTIN	4013288106896
Item class	63H

Description

Version:

Single piece, i.e. shank and tip of one piece. Shanks for direct fitting in electric screwdrivers. The tapered Torx® “HF” profile reliably retains all Torx® screws. Colour coded with a gold surface coating. Size TX40 with hexagonal blade through to the end of the handle.

Application:

Bit retainer function for optimum starting and tightening of Torx® screws.

Standard:

DIN ISO 1173

Material:

Chrome vanadium special alloy, high strength.
overall length: 50 mm

Technical description

Torx® profile	TX10
overall length	50 mm
Bit hexagon shank	E 6,3
Manufacturer's designation	867/4 TORX® HF
Drive profile	Screwdriver for TORX® screws
Type of product	Bit tool

