



Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 60mm



Order data

Order number	754700 60
GTIN	7610733003495
Item class	73B

Description

Version:

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard).

With handle of American hickory wood.

Dead-blow due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

Technical description

Head length with inserts	120 mm
Weight	1.47 kg
Material of body	Steel
Material of the handle	Hickory wood
Hammer head Ø	60 mm
Handle length	360 mm

Overall length	420 mm
Material of insert	Nylon, white
dead-blow	yes
Type of product	Hammer

Accessories

Spare insert, nylonconvex Hammer head Ø 60 mm	754730 60
Spare insert, nylonflat Hammer head Ø 60 mm	754720 60
Hickory hammer handle with wedge for head Ø 60 mm	754840 60