

Cotton gloves set, Glove size: 10



Order data

Order number	094200 10
GTIN	4029201131456
Item class	09H

Description

Version:

Gloves **for low-hazard areas** and **assembly work**, for protection against grazes, blisters and dirt. Lightweight **knitted cotton-gloves with fourchettes**, suitable also for wearing under other gloves.

Application:

Clean dry areas; precision assembly; electronics and Installation work.

Washing: Hand washing

Colour: white

Technical description

Wet grip	not available
EN 388 tear propagation resistance	not available
Glove size	10
EN 388 penetration resistance	not available
Accuracy of fit	good
EN 388 cut resistance	not available

Oil grip	not available
Breathability	very good
Touch sensitivity	very good
Set contents	12
EN 388 abrasion resistance	not available
Heat protection	not available
Protection category	Category II
Type of glove	Cotton gloves
Glove characteristics	Silicone-free
Glove characteristics	free of latex
Glove characteristics	DMF-free
Washing	Hand washing
Drying	dry
Length	260 mm
Application	reusable
Contents	12 pair
Colour	white
Application range	Precision
Backing material	Cotton
Coating variant	No coating
Weight	13 g
Material	Cotton
Type of product	Cotton gloves