

Garant**Soft-faced hammer with nylon inserts and steel central part, Hammer head Ø: 40mm****Order data**

Order number	754120 40
GTIN	4045197680433
Item class	71D

Description**Version:**

Sturdy metal central piece with handle of hickory, with nylon handle protection sleeve and ring wedge. The nylon inserts are impact resistant and wear-resistant, and are attached to the central piece by a double action system.

Central piece of steel.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

Spare nylon insert available under No. 754180 and spare handle available under No. 751650.

Technical description

Weight	0.578 kg
Handle length	320 mm
Head length with inserts	105 mm
Hammer head Ø	40 mm
Type of product	Hammer

Accessories

Spare nylon insert, piece Hammer head Ø 40 mm

754180 40

Hickory hammer handle with protective sleeve and ring
wedge Handle length 320 mm

751650 320