



Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 22mm



Order data

| | |
|--------------|---------------|
| Order number | 754700 22 |
| GTIN | 7610733003433 |
| Item class | 73B |

Description

Version:

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard).

With handle of American hickory wood.

Dead-blow due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

Technical description

| | |
|--------------------------|--------------|
| Head length with inserts | 75 mm |
| Handle length | 250 mm |
| Overall length | 270 mm |
| Material of body | Steel |
| Hammer head Ø | 22 mm |
| Material of the handle | Hickory wood |

| | |
|--------------------|--------------|
| Weight | 0.167 kg |
| Material of insert | Nylon, white |
| dead-blow | yes |
| Type of product | Hammer |

Accessories

| | |
|---|-----------|
| Hickory hammer handle with wedge for head Ø 22 mm | 754840 22 |
| Spare insert, nylonconvex Hammer head Ø 22 mm | 754730 22 |
| Spare insert, nylonflat Hammer head Ø 22 mm | 754720 22 |