



Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 27mm



Order data

Order number	754700 27
GTIN	7610733003440
Item class	73B

Description

Version:

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard).

With handle of American hickory wood.

Dead-blow due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

Technical description

Handle length	265 mm
Material of body	Steel
Weight	0.274 kg
Hammer head Ø	27 mm
Head length with inserts	90 mm
Material of the handle	Hickory wood

Overall length	290 mm
Material of insert	Nylon, white
dead-blow	yes
Type of product	Hammer

Accessories

Spare insert, nylonflat Hammer head Ø 27 mm	754720 27
Hickory hammer handle with wedge for head Ø 27 mm	754840 27
Spare insert, nylonconvex Hammer head Ø 27 mm	754730 27