



## Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 32mm



### Order data

Order number	754700 32
GTIN	7610733003457
Item class	73B

### Description

#### Version:

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard).

With handle of American hickory wood.

**Dead-blow** due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

#### Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

#### Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

### Technical description

Handle length	285 mm
Overall length	320 mm
Hammer head Ø	32 mm
Material of the handle	Hickory wood
Head length with inserts	100 mm
Material of body	Steel

Weight	0.391 kg
Material of insert	Nylon, white
dead-blow	yes
Type of product	Hammer

---

## Accessories

Spare insert, nylonflat Hammer head Ø 32 mm	754720 32
Spare insert, nylonconvex Hammer head Ø 32 mm	754730 32
Hickory hammer handle with wedge for head Ø 32 mm	754840 32