



## Plug-in ratchet reversible, Type-Square drive: 2-1/2in



### Order data

Order number	657600 2-1/2
GTIN	4018754034536
Item class	63A

### Description

#### Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

#### Plug-in reversible ratchet.

#### Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

#### Suitable for:

Torque wrench with rectangular sockets.

#### Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

---

## Technical description

Long-term rated loading	300 Nm
Plug-in shank	14×18 mm
Width b	43 mm
Height h	26 mm
No. of teeth	60
Square drive	1/2 in
Pitch S	25 mm
Exchangeable tool	Plug-in head
Ratchet reversible	yes
Ratchet with ejector	no
Type of product	Ratchet