



## Heavy-duty combi pliers, polished, overall length: 225mm



### Order data

Order number	700440 225
GTIN	4003773013198
Item class	73F

### Description

#### Version:

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire.

Jaws chemically blacked, polished head, plastic coated handles.

#### Standard:

**DIN ISO 5746.**

#### Material:

Special tool steel, drop-forged, and oil-hardened.

Cutting capacity hard wire up to  $\varnothing$ : 3 mm

Cutting capacity piano wire up to  $\varnothing$ : 2.5 mm

### Technical description

Cutting capacity piano wire up to $\varnothing$	2.5 mm
overall length	225 mm
Cutting capacity hard wire up to $\varnothing$	3 mm
Standard	DIN ISO 5746
Handle	plastic coated
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel
Surface	chemically blacked, head bright polished

non-sparking	no
Type of product	Multi-function pliers