

**Garant**
**Precision circlip pliers set, 4 pieces for internal circlips, Number of pliers: 4**

**Order data**

Order number	700132 4
GTIN	4045197524850
Item class	71A

**Description**
**Version:**

Forged grip and joint, precision made tips of special steel, special precision profile, pressed into the body. Pliers black, head ground, plastic coated handles.

**Advantage:**

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

**Standard:**

**DIN 5256 C** – für Innensicherungsringe.

**Supplied with:**

1 each circlip pliers No. 719770 size J1; J2; J3; J4.

**Technical description**

Tip Ø	1.25; 1.8; 2.25; 3.2; mm
for internal circlip Ø	12 – 25; 19 – 60; 40 – 100; 85 – 140 mm
Number of pliers	4
maximum overall length	140; 180; 225; 320 mm
Use of circlip pliers	Inner ring, straight

Standard	DIN 5256 C
Type of product	Circlip Pliers

---

## Accessories

Precision circlip pliers Type J3	719770 J3
Precision circlip pliers Type J4	719770 J4
Precision circlip pliers Type J2	719770 J2
Precision circlip pliers Type J1	719770 J1