



Plug-in ratchet reversible with QuickRelease ejector, Type-Square drive: 1-1/4in



Order data

Order number	657590 1-1/4
GTIN	4018754139606
Item class	63A

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Plug-in reversible ratchet with ejector. With reversing lever.

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

Technical description

Height h	14.5 mm
Width b	22 mm
Plug-in shank	9×12 mm
Long-term rated loading	40 Nm
No. of teeth	22
Series	725QR
Square drive	1/4 in
Pitch S	17.5 mm
Exchangeable tool	Plug-in head
Ratchet reversible	yes
Ratchet with ejector	yes
Type of product	Ratchet