



## High-power ring light with segment control, Ring lamp Ø: 66mm



### Order data

Order number	492225 66
GTIN	2050002067424
Item class	49K

### Description

**Version:**

LED ring light with integral controller for user-friendly operation – no separate control unit necessary. Ergonomic and intuitive to use for left and right-handed users. 2 working distances can be set (45 – 130 mm and 80 – 300 mm). Homogeneous illumination. Segments can be adjusted individually. Memory function for the preferred setting. Can be integrated into an ESD environment.

**Advantage:**

- **Multiple working distances can be set**
- **No external control unit required**
- **Flexible and intelligent segment control**

**Supplied with:**

Supplied with an adapter Ø 66 mm to 58 mm, international power supply unit (100 – 240 V), hexagon key L-wrench.

**Optional extras:**

Diffusor, polarisation filter, adapter for lenses

### Technical description

Power supply	Mains operated
Ring lamp Ø	66 mm
Ring lamp height	31 mm

Ring light width	128 mm
Ring light length	107 mm
electrostatic characteristic	EGB/ESD
Type of product	Lighting unit for measuring tool