

**Garant**

**Heavy-duty combination pliers, chrome-plated, with two-component grips, overall length: 200mm**


**Order data**

Order number	700340 200
GTIN	4045197416933
Item class	71B

**Description**
**Version:**

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

**Standard:**

**DIN ISO 5746.**

**Material:**

Special tool steel, drop-forged, and oil-hardened.

**Technical description**

Cutting capacity hard wire up to Ø	2.8 mm
overall length	200 mm
Cutting capacity piano wire up to Ø	2.2 mm
Standard	DIN ISO 5746
Handle	Multi-component covering with non-slip Haptoprene surface
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel

Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers