



## Plug-in ratchet reversible with QuickRelease ejector, Type-Square drive: 2-1/2in



### Order data

Order number	657590 2-1/2
GTIN	4018754139637
Item class	63A

### Description

#### Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

#### Plug-in reversible ratchet with ejector.

#### Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

$L$  = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

#### Suitable for:

Torque wrench with rectangular sockets.

#### Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

---

## Technical description

Plug-in shank	14×18 mm
Long-term rated loading	200 Nm
Height h	22.3 mm
Width b	41 mm
No. of teeth	36
Series	725QR/20
Square drive	1/2 in
Pitch S	38.5 mm
Exchangeable tool	Plug-in head
Ratchet reversible	yes
Ratchet with ejector	yes
Type of product	Ratchet