



Heavy-duty combi pliers, chrome-plated, with grips, overall length: 180mm



Order data

Order number	700400 180
GTIN	4003773043072
Item class	73F

Description

Version:

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire.

Jaws chrome-plated, handles with multi-component covering.

Standard:

DIN ISO 5746.

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

Cutting capacity piano wire up to Ø	2 mm
overall length	180 mm
Cutting capacity hard wire up to Ø	2.5 mm
Standard	DIN ISO 5746
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel
Surface	chrome-plated
non-sparking	no

Type of product

Multi-function pliers