



Plug-in ratchet slim with recessed reverser, Type-Square drive: 2-3/8in



Order data

Order number	657640 2-3/8
GTIN	4000896179695
Item class	630

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Slim plug-in ratchet with recessed reverser.

Material:

Chrome vanadium steel, chrome-plated.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Further plug-in heads with rectangular plug-in shank 22 × 28 mm available on request.

Technical description

Long-term rated loading	200 Nm
Height h	14.3 mm
Plug-in shank	14×18 mm
Width b	40 mm
No. of teeth	40
Square drive	3/8 in
Pitch S	36 mm
Exchangeable tool	Plug-in head
Material	Chrome vanadium steel
Type of product	Ratchet