



Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone, Cross-head size / overall length: 1/25mm



Order data

Order number	675220 1/25
GTIN	4013288191663
Item class	63H

Description

Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

With torsion zone, **toughened**. The torsion zone absorbs the peaks of force when screw driving. This protects the screw profile and achieves longer tool life (apart from size TX40).

Application:

For Phillips cross-head screws to DIN 3128 and DIN ISO 2351-2.

Standard:

DIN ISO 1173.

Material:

Chrome vanadium special alloy, **toughened**.

Technical description

overall length	25 mm
Cross-head size	1
Bit hexagon shank	C 6,3
Manufacturer's designation	855/1 TZ PZ
Standard	DIN ISO 1173
Drive profile	Pozidriv screwdriver
Colour coding	yes

Type of product

Bit tool