



## Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone, Cross-head size / overall length: 3/25mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 675220 3/25   |
| GTIN         | 4013288014825 |
| Item class   | 63H           |

### Description

#### Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

With torsion zone, **toughened**. The torsion zone absorbs the peaks of force when screw driving. This protects the screw profile and achieves longer tool life (apart from size TX40).

#### Application:

For Phillips cross-head screws to DIN 3128 and DIN ISO 2351-2.

#### Standard:

DIN ISO 1173.

#### Material:

Chrome vanadium special alloy, **toughened**.

### Technical description

|                            |                      |
|----------------------------|----------------------|
| Cross-head size            | 3                    |
| overall length             | 25 mm                |
| Bit hexagon shank          | C 6,3                |
| Manufacturer's designation | 855/1 TZ PZ          |
| Standard                   | DIN ISO 1173         |
| Drive profile              | Pozidriv screwdriver |
| Colour coding              | yes                  |

Type of product

Bit tool