

**Measuring probes, flexible, Type: K27****Order data**

Order number	478485 K27
GTIN	2050002080409
Item class	47F

Description**Version:**

Various measuring probes are available for different measurement ranges. These allow measurement into deep recesses where the tip is out of sight. The tactile procedure offers the facility to measure contours within gaps, irrespective of the material and surface characteristics. For special applications, other types of angled measuring probes are available in various widths and lengths, with a flexible shank or swan neck. The spectrum of the measurement range lies between 0.2 – 20 mm for widths from 3 – 12.7 mm.

Technical description

Length	85 mm
Shank length	70 mm
Sensor type	Standard probes, double ended
Width	9.5 mm
Cable length	500 mm
Measuring range	0.7 - 3.5 mm
Shank Ø	12 mm
Accuracy	±50 µm
Type of product	Measuring sensor