

Garant**Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 27 mm****Order data**

Order number	754750 27
GTIN	4045197923530
Item class	71D

Description**Version:**

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard). **Dead-blow** due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

With handle of American hickory wood.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

Head length with inserts: 90 mm

Handle length: 265 mm

Overall length: 290 mm

Weight: 0.274 kg

Technical description

Weight	0.274 kg
Handle length	265 mm
Hammer head Ø	27 mm
Head length with inserts	90 mm

Overall length	290 mm
Type of product	Hammer

Accessories

Spare insert, nylonflat Hammer head Ø 27 mm	754720 27
Hickory hammer handle with wedge for head Ø 27 mm	754840 27
Spare insert, nylonconvex Hammer head Ø 27 mm	754730 27