

HALDER**Dead-blow hammer with hickory handle, Hammer head Ø: 40mm****Order data**

Order number	755100 40
GTIN	4030618301615
Item class	73W

Description**Version:**

Sturdy steel T-piece with exchangeable top quality wear-resistant nylon faces. **Dead-blow** effect achieved by steel ball filling in hammer head.

Handle of premium quality hickory wood.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare nylon face see No. 754910.

See No. 755140 for spare blade.

Technical description

Material of the handle	Hickory wood
Head length with inserts	115 mm
Overall length	360 mm
Hammer head Ø	40 mm
Material of body	Steel tube
Weight	0.715 kg
Series	SUPERCRAFT®
Material of insert	Nylon, white, hard
Manufacturer's designation	SUPERCRAFT

Securing of body handle	Aluminium wedge and retaining pin
Surface	Powder coated
dead-blow	yes
Type of product	Hammer

Accessories

Spare insert, nylon Hammer head Ø 40 mm	754910 40
Hickory hammer handle for Hammer head Ø 40+50 mm	755140 40+50