



## PrecisionBit for Pozidriv, 1/4 inch C 6.3, Cross-head size / overall length: 3/25mm



### Order data

Order number	675285 3/25
GTIN	7610733211364
Item class	63E

### Description

#### Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

Distinctive elasticity and toughness combined with high hardness for a long tool life. High precision drive bits for perfect seating in the screw head and "Anti-cam-out". The "Nanotech" colour coating is both a **colour code** and an attractive **anti-rust protection**.

#### Application:

For Phillips cross-head screws to DIN 3128 and DIN ISO 2351-2.

#### Standard:

DIN ISO 1173.

#### Material:

High-tensile special steel combining maximum hardness and special toughness.

### Technical description

overall length	25 mm
Cross-head size	3
Bit hexagon shank	C 6,3
Manufacturer's designation	PrecisionBits
Standard	DIN ISO 1173
Drive profile	Pozidriv screwdriver

Type of product

Bit tool