

ejendals

Pair of gloves Tegera® 8800 Infinity, Glove size: 10



Order data

Order number	094364 10
GTIN	7340118318462
Item class	04R

Description

Version:

Tegera® 8800 Infinity. Particularly light-weight precision gloves with nitrile-PU coating suitable for dry and slightly humid workplaces.

Multi-purpose gloves of the new Infinity range with **outstanding touch sensitivity** and good grip capability. With oil- and grease-resistant palms. Resistant to **contact heat up to 100 °C**.

Standard:

EN 407

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
Colour: black/yellow

Technical description

Glove size	10
Series	Tegera®
Protection category	Category II
Type of glove	Multi-purpose gloves

Pack unit quantity	6
EN 388:2016	4121X
EN 407	X1XXXX
Backing material	Nylon Spandex
Coating	Nitrile, PU
Application range	Precision
Colour	black/yellow
Type of product	Multi-purpose gloves