

## ejendals

### Pair of gloves Tegera® 8802 Infinity, Glove size: 11



#### Order data

Order number	094365 11
GTIN	7340118318837
Item class	04R

#### Description

**Version:**

**Multi-purpose gloves** of the new Infinity range with **outstanding touch sensitivity** and good grip capability. With oil- and grease-resistant palms. Resistant to **contact heat up to 100 °C**. Tegera® 8802 Infinity. Sturdy assembly gloves with dense double coating of nitrile and nitrile foam with water-based PU, suitable for damp and slightly oily working areas.

**Standard:**

EN 407

EN 388; EN 420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Knitted technology: 18G

Colour: black / yellow

#### Technical description

Glove size	11
Series	Tegera®
Type of glove	Multi-purpose gloves

Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	6
Glove characteristics	Foodstuffs certified
Glove characteristics	DMF-free
EN 388:2016	4121X
EN 407	X1XXXX
Backing material	Nylon
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Colour	black / yellow
Knitted technology	18G
Contact heat up to	100 °C
Application	reusable
Type of product	Multi-purpose gloves