

**PrecisionBit for slot-head, 1/4 inch C 6.3, Blade width: 4mm****Order data**

Order number	675300 4
GTIN	7610733211579
Item class	63E

Description**Version:**

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

Distinctive elasticity and toughness combined with high hardness for a long tool life. High precision drive bits for perfect seating in the screw head and "Anti-cam-out". The "Nanotech" colour coating is both a **colour code** and an attractive **anti-rust protection**.

Application:

For slot-head screws to DIN 3127 and DIN ISO 2351-1.

Standard:

DIN ISO 1173.

Material:

High-tensile special steel combining maximum hardness and special toughness.

Technical description

Cutter thickness	0.6 mm
Blade width	4 mm
overall length	25 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	PrecisionBits
Drive profile	Slot-head screwdriver
Type of product	Bit tool

