

HALDER**Dead-blow hammer with hickory handle, Hammer head Ø: 60mm****Order data**

Order number	755100 60
GTIN	4030618301646
Item class	73W

Description**Version:**

Sturdy steel T-piece with exchangeable top quality wear-resistant nylon faces. **Dead-blow** effect achieved by steel ball filling in hammer head.

Handle of premium quality hickory wood.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare nylon face see No. 754910.

See No. 755140 for spare blade.

Technical description

Head length with inserts	145 mm
Hammer head Ø	60 mm
Overall length	370 mm
Material of body	Steel tube
Weight	1.7 kg
Material of the handle	Hickory wood
Series	SUPERCRAFT®
Material of insert	Nylon, white, hard
Manufacturer's designation	SUPERCRAFT

Securing of body handle	Aluminium wedge and retaining pin
Surface	Powder coated
dead-blow	yes
Type of product	Hammer

Accessories

Hickory hammer handle for Hammer head Ø 60+70 mm	755140 60+70
Spare insert, nylon Hammer head Ø 60 mm	754910 60