



PrecisionBit for slot-head, 1/4 inch, 25 mm long, Blade width: 5,5 mm



Order data

Order number	675300 5,5
GTIN	7610733211586
Item class	63E

Description

Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

Distinctive elasticity and toughness combined with high hardness for a long tool life. High precision drive bits for perfect seating in the screw head and "Anti-cam-out". The "Nanotech" colour coating is both a **colour code** and an attractive **anti-rust protection**.

Application:

For slot-head screws to DIN 3127 and DIN ISO 2351-1.

Standard:

DIN 3126 C 6,3 (1/4 Zoll).

Material:

High-tensile special steel combining maximum hardness and special toughness.

Cutter thickness: 0.8 mm

overall length: 25 mm

Technical description

overall length	25 mm
Blade width	5.5 mm
Cutter thickness	0.8 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	PrecisionBits
Drive profile	Slot-head screwdriver

Type of product

Bit tool