



Clear view flap disc SLTR Control, (ZA) for steel and stainless steels, Ø 125 mm, Grit: 40



Order data

Order number	565446 40
GTIN	4027497579389
Item class	53L

Description

Version:

Abrasive flap disc with **field of view**, permitting a view of the workpiece. Very high coating density and long service life.

Application:

Ideal for precision abrasive work.

Technical description

Grit	40
Shape description	dished with overlap between strips
Disc Ø	125 mm
Bore Ø	22.23 mm
Grinding media	Zirconium aluminium oxide (ZA)
Grinding medium code	ZA

Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
See-through grinding	yes
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		