

Garant**Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 50 mm****Order data**

Order number	754750 50
GTIN	4045197923561
Item class	71D

Description**Version:**

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard). **Dead-blow** due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

With handle of American hickory wood.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

Head length with inserts: 110 mm

Handle length: 335 mm

Overall length: 385 mm

Weight: 1.05 kg

Technical description

Hammer head Ø	50 mm
Overall length	385 mm
Weight	1.05 kg
Handle length	335 mm

Head length with inserts	110 mm
Type of product	Hammer

Accessories

Spare insert, nylonflat Hammer head Ø 50 mm	754720 50
Hickory hammer handle with wedge for head Ø 50 mm	754840 50
Spare insert, nylonconvex Hammer head Ø 50 mm	754730 50