



Combination pliers, chrome-plated VDE dip insulated, overall length: 200mm



Order data

Order number	701735 200
GTIN	4003773015321
Item class	73F

Description

Version:

Special tool steel; serrated jaws. **Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V. Cutting edges additionally induction hardened (approx. 60 HRC).

Jaws chrome-plated, plastic coated handles, **dip insulated**.

Standard:

DIN ISO 5746.

Technical description

Cutting capacity hard wire up to Ø	2.5 mm
overall length	200 mm
Cutting capability medium hard wire up to Ø	3.8 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	dip insulated
Material	Special tool steel
Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers

