

**Heavy-duty combination pliers ERGO™, overall length: 160mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 701640 160    |
| GTIN         | 7314150101863 |
| Item class   | 730           |

**Description****Version:**

Chrome vanadium steel, chrome-plated head and joint. Slim, rounded jaws; serrated inside. Heavy-duty grips with **opening spring that can be engaged / disengaged**. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire.

**Standard:**

**DIN ISO 5746.**

**Technical description**

|   |                       |
|---|-----------------------|
| Cutting capacity hard wire up to $\varnothing$  | 2 mm                  |
| Cutting capacity piano wire up to $\varnothing$ | 1.8 mm                |
| overall length                                  | 160 mm                |
| Standard  | DIN ISO 5746          |
| Material  | Chrome vanadium steel |
| Surface   | chrome-plated         |

|                 |                       |
|-----------------|-----------------------|
| non-sparking    | no                    |
| Type of product | Multi-function pliers |