

Garant
Heavy duty combination pliers, chrome-plated VDE insulated, overall length: 200mm

Order data

Order number	701910 200
GTIN	4045197501455
Item class	71B

Description
Version:

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire. Insulated to **DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:

DIN ISO 5746.

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

Cutting capacity piano wire up to Ø	2.2 mm
Cutting capacity hard wire up to Ø	2.8 mm
overall length	200 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	Multi-component covering with non-slip Haptoprene surface
Material	Special tool steel

Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers