



## Vanadium steel combination pliers, chrome-plated VDE insulated, overall length: 190mm



### Order data

Order number	701800 190
GTIN	4003773040415
Item class	73F

### Description

#### Version:

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire. **For working at voltages up to 1000 V to DIN EN IEC 60900 / VDE 0682-201.**

Pliers chrome-plated, handles with multi-component covering.

#### Standard:

**DIN ISO 5746**

### Technical description

Cutting capacity piano wire up to Ø	2 mm
Cutting capacity hard wire up to Ø	2.5 mm
overall length	190 mm
electrostatic characteristic	VDE 1000 V
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Jaw characteristics	serrated
Handle	Multi-component covering
Material	Chrome vanadium steel
Surface	chrome-plated

non-sparking	no
Type of product	Multi-function pliers