

**Heavy duty combination pliers, offset VDE insulated, overall length: 190mm****Order data**

Order number	701950 190
GTIN	4007582007447
Item class	76B

Description**Version:**

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire. Handles with thick-walled grips **insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V**. Offset design for improved ergonomics and a clear view of the working area.

Standard:

DIN ISO 5743

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

Cutting capacity piano wire up to Ø	2 mm
overall length	190 mm
Cutting capacity hard wire up to Ø	2.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5743
Material	Special tool steel
non-sparking	no
Type of product	Multi-function pliers

