

**HALDER****Dead-blow hammer with hickory handle, Hammer head Ø: 30mm****Order data**

Order number	755100 30
GTIN	4030618301592
Item class	73W

**Description****Version:**

Sturdy steel T-piece with exchangeable top quality wear-resistant nylon faces. **Dead-blow** effect achieved by steel ball filling in hammer head.

Handle of premium quality hickory wood.

**Application:**

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

**Spare part:**

For spare nylon face see No. 754910.

See No. 755140 for spare blade.

**Technical description**

Hammer head Ø	30 mm
Head length with inserts	110 mm
Weight	0.46 kg
Material of body	Steel tube
Material of the handle	Hickory wood
Overall length	330 mm
Series	SUPERCRAFT®
Material of insert	Nylon, white, hard
Manufacturer's designation	SUPERCRAFT

Securing of body handle	Aluminium wedge and retaining pin
Surface	Powder coated
dead-blow	yes
Type of product	Hammer

---

## Accessories

Spare insert, nylon Hammer head Ø 30 mm	754910 30
Hickory hammer handle for Hammer head Ø 30+35 mm	755140 30+35