



Grooved water pump pliers, chrome-plated, with grips, overall length: 250 mm



Order data

Order number	705200 250
GTIN	4003773043836
Item class	73F

Description

Version:

The clamping pressure acts only on the **grooved sliding joint** which has multiple adjustment positions; hence no slipping and no wear on the screw. Designed to prevent fingers being trapped. Self-tightening on pipes and nuts. With notched serrated gripping jaws, induction hardened.

Jaws chrome-plated, handles with multi-component covering.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

Hexagon across flats: 36 mm

Jaw capacity for pipes: 1.5/16 inch

Technical description

overall length	250 mm
Jaw capacity for pipes	1.5/16 inch
Hexagon across flats	36 mm
Handle	Multi-component covering
Surface	chrome-plated
Standard	DIN ISO 8976
non-sparking	no

Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers