



Ring plug-in head, Type-Width across flats: 2-15mm



Order data

| | |
|--------------|---------------|
| Order number | 657900 2-15 |
| GTIN | 4018754034215 |
| Item class | 63A |

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Technical description

| | |
|----------------------------|-------------------|
| Plug-in shank | 14×18 mm |
| Width b | 24 mm |
| Width across flats | 15 mm |
| Height h | 11 mm |
| Pitch S | 25 mm |
| Exchangeable tool | Plug-in head |
| Tool with ratchet function | no |
| Type of product | Ring plug-in head |