



Heavy duty combination pliers, chrome-plated VDE insulated, overall length: 180mm



Order data

Order number	701900 180
GTIN	4003773010012
Item class	73F

Description

Version:

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire. Insulated to **DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

Jaws chrome-plated, handles with multi-component covering.

Standard:

DIN ISO 5746.

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

overall length	180 mm
Cutting capacity piano wire up to Ø	2 mm
Cutting capacity hard wire up to Ø	2.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	Multi-component covering
Material	Special tool steel
Surface	chrome-plated

non-sparking	no
Type of product	Multi-function pliers