

**Garant****Vanadium steel combination pliers, chrome-plated VDE insulated, overall length: 160mm****Order data**

Order number	701710 160
GTIN	4045197501400
Item class	71B

**Description****Version:**

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire. **For working at voltages up to 1000 V to DIN EN IEC 60900 / VDE 0682-201.**

Pliers chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

**Standard:****DIN ISO 5746****Technical description**

Cutting capacity piano wire up to Ø	1.5 mm
Cutting capacity hard wire up to Ø	2 mm
overall length	160 mm
electrostatic characteristic	VDE 1000 V
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Jaw characteristics	serrated
Handle	Multi-component covering with non-slip Haptoprene surface

Material	Chrome vanadium steel
Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers