

**Vanadium combination pliers, bright finished, overall length: 200mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 703000 200    |
| GTIN         | 4045197282576 |
| Item class   | 72B           |

**Description****Version:**

Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); suitable even for piano wire.

Jaws bright finished, plastic coated handles.

**Standard:**

**DIN ISO 5746**

**Material:**

Chrome vanadium steel, drop forged.

**Technical description**

|                                     |  |
|-------------------------------------|--|
| Cutting capacity hard wire up to Ø  | 2.5 mm   |
| overall length                      | 200 mm   |
| Cutting capacity piano wire up to Ø | 2 mm   |
| Standard                            | DIN ISO 5746   |
| Jaw characteristics                 | inner face serrated  |
| Handle                              | plastic coated   |
| Manufacturing process               | Cutting edges induction hardened (approx. 64 HRC), pliers body drop forged |
| Material                            | Chrome vanadium steel  |
| Surface                             | bright finish  |

|                 |                       |
|-----------------|-----------------------|
| non-sparking    | no                    |
| Type of product | Multi-function pliers |