

Garant
Vanadium steel combination pliers, chrome-plated VDE insulated, overall length: 200mm

Order data

Order number	701710 200
GTIN	4045197501431
Item class	71B

Description
Version:

Chrome vanadium steel. Serrated jaws. Cutting edges additionally induction hardened (approx. 64 HRC); also suitable for piano wire. **For working at voltages up to 1000 V to DIN EN IEC 60900 / VDE 0682-201.**

Pliers chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:
DIN ISO 5746
Technical description

overall length	200 mm
Cutting capacity piano wire up to \varnothing	2 mm
Cutting capacity hard wire up to \varnothing	2.5 mm
electrostatic characteristic	VDE 1000 V
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Jaw characteristics	serrated
Handle	Multi-component covering with non-slip Haptoprene surface

Material	Chrome vanadium steel
Surface	chrome-plated
non-sparking	no
Type of product	Multi-function pliers