



## Heavy duty combination pliers, chrome-plated VDE insulated, overall length: 225mm



### Order data

Order number	701900 225
GTIN	4003773010036
Item class	73F

### Description

#### Version:

Considerable cutting performance with little effort. Serrated jaws. Cutting edges additionally induction hardened (approx. 63 HRC); also suitable for piano wire. Insulated to **DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

Jaws chrome-plated, handles with multi-component covering.

#### Standard:

**DIN ISO 5746.**

#### Material:

Special tool steel, drop-forged, and oil-hardened.

### Technical description

overall length	225 mm
Cutting capacity piano wire up to Ø	2.5 mm
Cutting capacity hard wire up to Ø	3 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5746
Handle	Multi-component covering
Material	Special tool steel
Surface	chrome-plated

non-sparking	no
Type of product	Multi-function pliers