

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 4/S4mm

Order data

Order number	268717 4/S4
GTIN	4045197923714
Item class	21V

Technical description

Pack of insert screws	269028 10
Clamping height L_2	3.58 mm
suitable indexable insert	CDCT S4010.
Overhang L_1	12 mm
Insert size	4 mm
Minimum pre-drill $\varnothing D_{min}$	4.57 mm
Centre offset L_3	2.41 mm
Overall length L	65 mm
ISO code toolholder	A04X SCLDR/LS4
Setting angle κ	97 degrees
Shank $\varnothing D_s$	4 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200