

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 5/S4mm

Order data

Order number	268717 5/S4
GTIN	4045197923721
Item class	21V

Technical description

Overall length L	65 mm
Centre offset L ₃	2.95 mm
Overhang L ₁	15 mm
suitable indexable insert	CDCT S4010.
Insert size	4 mm
Clamping height L ₂	4.6 mm
Minimum pre-drill \varnothing D _{min}	5.78 mm
Pack of insert screws	269028 10
Setting angle κ	95 degrees
ISO code toolholder	A05X SCLDR/LS4
Shank \varnothing D _s	5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200