

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 4/S4mm**

**Order data**

Order number	268718 4/S4
GTIN	4045197923752
Item class	21V

**Technical description**

ISO code toolholder	A04X SCLDR/LS4
Overhang $L_1$	12 mm
Centre offset $L_3$	2.41 mm
suitable indexable insert	CDCT S4010.
Minimum pre-drill $\varnothing D_{\min}$	4.57 mm
Clamping height $L_2$	3.58 mm
Setting angle $\kappa$	97 degrees
Pack of insert screws	269028 10
Insert size	4 mm
Overall length L	65 mm
Shank $\varnothing D_s$	4 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200